



TRISEP® ACM1

High Rejection RO Membrane

TRISEP® ACM1 flat sheet is a high rejection reverse osmosis membrane that is versatile enough to be used in a wide variety of water purification and process applications. ACM1 offers very high rejection and is a direct replacement for competitive RO products. ACM1 membrane sheet is available in both dry and wet flat sheet rolls and is FDA compliant.

MEMBRANE CHARACTERISTICS

Membrane Chemistry	Backing Material	Stabilized Salt Rejection (%)	Minimum Salt Rejection (%)
Thin-Film Polyamide	Non-Woven Polyester	99.5	99.0

Flux Range LMH (GFD) ^a	Thickness (µm)	pH Range	Chlorine Tolerance ^b
40.8 – 59.5 (24.0 – 35.0)	130 – 170	1.0 – 12.0	< 0.1 ppm

a Test conditions: 2,000 ppm NaCl, 15.5 bar (225 psi), 25°C (77°F), 15% recovery, pH 8.0, 30 minutes operation. Membrane specifications may change without notice as design revisions occur.

b Oxidizing agents, such as free chlorine, in contact with polyamide membranes may result in shortened operating life or membrane failure.

IMPORTANT INFORMATION

Standard Sizes: TRISEP flat sheet membrane is available in a sample size of 305 mm x 1,016 mm (12 in x 40 in) and in a nominal roll size of 305 m x 1,016 mm (1,000 ft x 40 in). Custom lengths may be available on request.

Initial Flush: MANN+HUMMEL Water & Fluid Solutions recommends flushing membrane for 30 minutes and discarding permeate during the flush prior to operation.

Storage: Membrane is shipped dry unless wet membrane is specifically requested. Membrane shipped dry should be stored in a cool, dry place. If shipped wet, TRISEP membrane must remain sealed and refrigerated prior to use. Please see Membrane Storage Guide – Flat Sheet Membrane (TSG-O-011).

Contact

Europe

Germany: +49 611 962 6001
Italy: +39 0721 1796201
info@microdyn-nadir.com

Americas

USA: +1 805 964 8003
sales.mnus@microdyn-nadir.com

Asia

Singapore: +65 6457 7533
China: +86 10 8413 9860
waterchina@mann-hummel.com